





LOC	DIST	REVISIONS			
FT	64	P	LTR	DESCRIPTION	DATE
		P		REV PER 0G3C-0104-01	05SEP01

D


C

B


A



SECTION A-A
ROTATED 90° CW
SCALE 10:1
FOR -6,-7 & -8 ONLY



1. RECEPTACLE ACCEPTS AN .008-.014 THK. I.C. LEAD.
2. TWO .000030 MIN.THK.GOLD STRIPES IN CONTACT AREA, TIN-LEAD(93-7) ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
3. TWO .000015 MIN.THK.GOLD STRIPES IN CONTACT AREA, TIN-LEAD(93-7) ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
4. TUBE LOADED.



SECTION A-A
ROTATED 90° CW
SCALE 10:1
FOR -1,-2 & -3 ONLY

4	OBSOLETE	TINNED	PHOS.BRZ.	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	2-643650-3
	OBSOLETE	TINNED	PHOS.BRZ.	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	643650-8
	OBSOLETE	4	BE.CU.	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	643650-7
		TINNED	BE.CU.	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	643650-6
SUPSD BY	643650-2	4	PHOS.BRZ.	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	643650-4
	OBSOLETE	TINNED	PHOS.BRZ.	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	643650-3
	OBSOLETE	4	BE.CU.	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	643650-2
		TINNED	BE.CU.	GLASS-FILLED THERMOPLASTIC, 94V-O, BLACK	643650-1
		CONTACT FINISH		CONTACT MAT'L	HOUSING MATERIAL
				PART NO.	
				THIS DRAWING IS A CONTROLLED DOCUMENT.	
				DWG M.CYRUS 6-1-84	
				CHK N.JONES 7-3-84	
				APVD J.GRAY 7-10-84	
				NAME	
				PRODUCT SPEC	
				108-1066	
				APPLICATION SPEC	
				114-1049	
				SIZE	
				CAGE CODE	
				DRAWING NO	
				RESTRICTED TO	
				A1 00779	
				C=643650	
				CUSTOMER DRAWING	
				SCALE 5:1	
				SHEET 1 OF 1	
				REV P	

D

C

B

A