



Mallory Sonalert Products, Inc.

Part #:

SCE028LD3MG4B

Sales Outline Drawing

Revision:

A

Specifications:

Sound Level Category:	Loud	Loud	Loud	Medium
Mode of Operation:	Continuous	Double Pulse	Quick Pulse	Dual Tone
Loudness @ 2 FT:	85 to 95 dB(A) Typ.	85 to 95 dB(A) Typ.	85 to 95 dB(A) Typ.	75 to 85 dB(A) Typ.
Pulse Rate (PPS):	N/A	2	60	1.5
Frequency:	2900 $\pm$ 500 Hz	2900 $\pm$ 500 Hz	2900 $\pm$ 500 Hz	3.0 - 2.9 kHz
Connection:	T-BLOCK ONLY	T-BLOCK AND BLACK WIRE TO (-)	T-BLOCK AND YELLOW WIRE TO (-)	T-BLOCK AND BOTH WIRES TO (-)
Voltage Rating:	16 to 28 VDC			
Current Draw:	40mA MAX			
Housing Material:	6/6 Nylon, Color: Black			
Storage Temperature:	-40° to +85° C			
Operating Temperature:	-40° to +85° C			
Panel Mounting:	Recommended hole size is 1.25"(31.75mm). Thread front will fit standard 30mm(1.181") hole.			
Knurled Nut:	Used to attach part to panel. The max recommended torque is 10 in-lbs.			
Weight (Typical):	1.6 oz (45g)			
NEMA 3R, 4X, & 12:	Approved with use of ACC03.			
cUL Recognition:	cUL Recognized			
Options:	Please contact factory.			

Dimensions: Inches (mm)

cUL Recognized

ROHS Compliant

