


181-4916 = 5520

## DO-IT-YOURSELF SMD GRABBER® TEST CLIP


The SMD Grabber® Test Clip is especially suited for testing surface mounted packages on centers as small as 0.76mm (.030). Pincer-like contact grasps individual legs of SMD's such as the SOIC, SOJ, PCC, etc. Its circular design and small size have been developed for easy use and handling.



MODEL  
5243-\*

LIST 16.50  
(Pkg. 10 per Color)

## DO-IT-YOURSELF SMD GRABBER® KITS



MODEL	Features	LIST per Kit
5231-*	Kit contains 2 pcs. of 5243.	3.55
5520	Kit contains 10 pcs. of 5243, one of each color.	14.85

\*STD COLORS: -02 one Black and one Red, -00 two Black, -11 two Brown, -22 two Red, -33 two Orange, -44 two Yellow, -55 two Green, -66 two Blue, -77 two Violet, -88 two Gray, -99 two White.

## DO-IT-YOURSELF MINIPINER® TEST CLIP


This clip utilizes a snap-on cap and a solder contact to provide reliable connections. The lower contact has a pincer type action ideally suited for testing standard DIP packages.

**MATERIAL:** Beryllium copper contact.

**FINISH:** Selectively gold plated.

**RATING:** 1000 WVDC; 5 Amps; +80°C. (+176°F.) Max.

\*STD. COLORS: -0 Black, -1 Brown, -2 Red, -3 Orange, -4 Yellow, -5 Green, -6 Blue, -7 Violet, -8 Gray, -9 White.



MODEL  
5418-\*

LIST 1.50

## DO-IT-YOURSELF MICROGRABBER® TEST CLIP


**MATERIAL:** Contact, beryllium copper.

**FINISH:** Gold plated.

**INSULATION:** Glass filled nylon.

**RATING:** 1000 WVDC, 3 Amps, +102°C. (+216°F.) Max.

\*STD COLORS: -0 Black, -1 Brown, -2 Red, -3 Orange, -4 Yellow, -5 Green, -6 Blue, -7 Violet, -8 Gray, -9 White.




MODEL  
4233-\*

(See assembly details, page 103.)

LIST 12.50 PKG  
(Pkg. Ten Per Color)

## DO-IT-YOURSELF MICROGRABBER® TEST CLIP KITS



MODEL	Features	LIST per Kit
4743-*	Kit contains 2 pcs. of 4233.	3.05
5524	Kit contains 10 pcs. of 4233, one of each color.	11.00

\*STD COLORS: -02 one Black and one Red, -00 two Black, -11 two Brown, -22 two Red, -33 two Orange, -44 two Yellow, -55 two Green, -66 two Blue, -77 two Violet, -88 two Gray, -99 two White.

## DO-IT-YOURSELF MINIGRABBER® TEST CLIP


**MATERIAL:** Contact, beryllium copper.

**FINISH:** Gold plated.

**INSULATION:** Glass filled nylon.

**RATING:** 3000 WVDC, 12 Amps, +102°C. (+216°F.) Max.

\*STD COLORS: -0 Black, -1 Brown, -2 Red, -3 Orange, -4 Yellow, -5 Green, -6 Blue, -7 Violet, -8 Gray, -9 White.



MODEL	"X" Dia.
3925-*	2.29 (.090)
4555-*	3.66 (.144)

(See assembly details, page 103.)

LIST 12.00 PKG  
(Pkg. Ten Per Color)