




Recommended Maximum Panel Thickness: .28" (7,0mm)

FEATURES:

- Ideal for panel mount applications.
- .079" (2mm) opening at bottom of jack enables solder type wire attachment.

MATERIALS:

Insulator & Collars: Nylon, Color Per Part Number

Banana Jack & Nut: Brass, Nickel Plated

RATINGS:

Operating Voltage: 750 VRMS Max.

Current: 20 Amperes Max.

ORDERING INFORMATION: Model 5933-*

* = Color Code, Standard Colors: -0 Black, -2 Red, -4 Yellow, -5 Green, -6 Blue, -9 White

Sold in packages of ten per color.

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[5933-6](#) [5933-0](#) [5933-9](#) [5933-4](#) [5933-5](#) [5933-2](#)