

**NOTE:** Unless otherwise stated, all items are Nickel Plated Brass with Delrin Insulators.

## BNC MALE, 2-Piece

with fixed center pin.  
Nickel plated body,  
delrin insulator,  
gold plated  
center pin



(Display pack of 1; for bulk add a "B" suffix, e.g. 920B)

| Wire Type                  | Part Number |
|----------------------------|-------------|
| RG59 & 62<br>PVC Jacket    | 980         |
| RG59 & 62<br>Teflon Jacket | 920         |
| RG58/U                     | 979         |
| RG6/U                      | 929         |

## BNC MALE, 3-Piece

with separate  
pin. Nickel plated body,  
delrin insulator, gold  
plated pins.



| Wire Type                        | Package Quantity | Part Number |
|----------------------------------|------------------|-------------|
| RG58/U<br>PVC                    | One Per          | 974         |
| RG58/U                           | Display Ten Pack | 974-10      |
| RG58A/U                          | One Per          | 996         |
| RG58<br>Teflon                   | One Per          | 997         |
| RG62 &<br>RG59/U<br>PVC          | One Per          | 973         |
| RG62<br>RG59/U                   | Display Ten Pack | 973-10      |
| RG59/U with<br>Teflon            | One Per          | 998         |
| RG59/U with<br>20 ga. pin        | One Per          | 994         |
| RG6/U<br>(.275" O.D.)            | One Per          | 989         |
| RG6/U<br>(.275" O.D.)            | Display Ten Pack | 989-10      |
| RG8X &<br>mini 8                 | One Per          | 926         |
| RG174,<br>179, 187,<br>188 & 316 | One Per          | 927         |

## BNC MALE, one-piece

with separate pin.  
Nickel plated body,  
delrin insulator, gold  
plated center pin.  
Packed 1 per blister; add "B" suffix for  
bulk packaging.



| Wire Type             | Part Number |
|-----------------------|-------------|
| RG58/U                | 964         |
| RG59/U                | 969NP       |
| RG6/U<br>(.275 O. D.) | 988         |

## Right Angle, BNC MALE



Handy in tight  
places. Conductors  
attach via screw  
connections. For  
coax under .275"



Such as RG58, 59, 62, 6

**No. 967**

## UG-88/U SCREW-CLAMP STYLE BNC MALE CONNECTOR



**No. 954NP** - For RG58/U

nickel plate,  
Delrin insulator

**No. 961NP** - For RG59/U

Nickel Plated, Delrin Insulator

**No. 975** - For RG6/U

For commercial RG6/U cable such as  
Belden type 9290 (dual braid, commercial  
type) etc. For cables with O.D. .275" to  
.290"

## One-Piece, Crimp Type BNC Male with Insulating Boot.

Separate center pin. Quick and  
weather tight. Nickel plated Brass,  
gold plated center pin.



| Wire Type          | Part Number |
|--------------------|-------------|
| RG59/U &<br>RG62/U | 938         |
| RG58/U             | 937         |

## BNC MALE RIGHT ANGLE

Crimp-on Two-piece connector for  
RG59/U and RG62/U cables.



**No. 980RA**

## BNC Center Contact Pins.

Bulk packed only.

| Wire Type   | Part Number |
|-------------|-------------|
| RG58/U      | RG58-PIN    |
| RG59/U      | RG59-PIN    |
| RG6         | RG6-PIN     |
| RG58/A      | RG58A-PIN   |
| RG59 20 Ga. | RG59L-PIN   |

## BNC Crimping Rings

Bulk packed only.

This series of rings are all  
1/2" in length.

| Wire Type | Part Number |
|-----------|-------------|
| RG58      | RG58-RING   |
| RG59      | RG59-RING   |
| RG6       | RG6-RING    |

**NOTE:** All connectors on this page are available in bulk. Add "B" to part no. when ordering.