

Protective covers - HC-B 32-TMS-SD-IP65 - 1580539

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

HEAVYCON ADVANCE B32 IP65 protective cover, for panel mounting side, screw locking with 2 Allen screws, with seal, 3 mm retaining cord eyelet



Key commercial data

Packing unit	1 PCE
Custom tariff number	85389099
Country of origin	Germany

Technical data

Ambient conditions

Schutzart Gehäuse (IP)	IP65
Ambient temperature (operation)	-20 °C ... 100 °C

General

Design	B32
Type	HC-ADVANCE protective cover
Color	gray
Locking type	Screw locking
Fixing screws	M6 (5 mm Allen screw)
Seal material	NBR
Material lock	High-grade steel
Material of locking screw	High-grade steel
Material, protective cover	ABS
Inflammability class according to UL 94	V0

Protective covers - HC-B 32-TMS-SD-IP65 - 1580539

Classifications

eCl@ss

eCl@ss 4.0	27141210
eCl@ss 4.1	27141210
eCl@ss 5.0	27149110
eCl@ss 5.1	27149110
eCl@ss 6.0	27261210
eCl@ss 7.0	27440208
eCl@ss 8.0	27440208

ETIM

ETIM 2.0	EC000241
ETIM 3.0	EC002040
ETIM 4.0	EC000723
ETIM 5.0	EC000723

UNSPSC

UNSPSC 6.01	30212113
UNSPSC 7.0901	39121712
UNSPSC 11	39121712
UNSPSC 12.01	39121712
UNSPSC 13.2	39121712

Drawings

Dimensioned drawing

