

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2008

© COPYRIGHT 2008

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
A1	-	-	-		-	-


ERGOCRIMP DIE SET FOR MCON 1.2 CLEAN BODY SWS

Matrize in Kombination mit Ergocrimp Basishandzange TE P/N 539635-1 verwenden
Use die in combination with Ergocrimp basis hand tool TE P/N 539635-1

Matrize im Karton mit Bedienungsanleitung 411-18491 verpackt
Die packed in a cardboard with instruction sheet 411-18491

3-1579001-9	1	6-0744013-2	Instruction Sheet	Bedienungsanleitung	6
	1	0-0519024-2	Nut M4 DIN 985	Mutter M4 DIN 985	5
	1	1-0519151-3	Screw M4x25	Schraube M4x25	4
	1	1-0519151-1	Screw M4x16	Schraube M4x16	3
	1	2-1579025-4	Locator Assembly	Drahtanschlag	2
	1	2-1579025-3	Contact Locator	Kontaktpositionierer	1
	QTY Stck	PN	Description	Benennung	Pos.

Kontakt	DGB (mm ²)	Drahtcrimp / Wire Crimp		Isolationscrimp / Insulation Crimp		Isol.Ø	Betriebsanl.
Contact	AWG	Hoehe/Height mm	Breite/Width mm	Hoehe/Height mm	Breite/Width mm	Ins.Range	Instr.Sheet
1418845	24	0,80 ±0,03	1.27 F	3.2	3.05 0	1.1-1.75	411-18491
	0,25	0,82 ±0,03					
	22	0,86 ±0,03					
	0,35	0,87 ±0,03					



THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN Ch. Witt	28MAY2008	tyco Electronics AMP GmbH D - 64625 Bensheim	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±1°	CHK -	-	NAME ERGOCRIMP DIE SET FOR MCON 1.2 CLEAN BODY SWS	
		APVD -	-		
		PRODUCT SPEC -	-	SIZE A3	
		APPLICATION SPEC -	-		
MATERIAL -	FINISH -	WEIGHT 200 g	CAGE CODE 00779	DRAWING NO C-3-1579001-9	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 2:1	SHEET 1 of 1	REV A