

CLED2D
(4) LED Flashlight**Specifications**



Designation:	Energizer Flashlight
Power Source:	Two D Size Batteries (ANSI/NEDA 13 Series)
Lamp:	LED (4) (Rated at 3.6V, 0.02A)
Lamp Life:	Rated at Lifetime
Lamp Output:	Rated at 5.6 Candela
Typical Weight:	150 grams (5.3 oz.) (without batteries)

Features

- (4) Superbright White LED's
- Soft Touch Rubber Jacket for Body and Lens Hood
- 2D Cells (extra long run time)
- New Reflector and Lens
- Modern Styling and Colors

Typical Battery Service

Continuous
at 21°C (70°F)

**Physical Dimensions**
mm (inches)**Typical Battery Service to end of useable light at 21°C (70°F)**

<u>Schedule</u>	<u>Battery Type</u>	<u>Hours (ON Time)</u>
Continuous	E95	50

Important Notice

This datasheet contains information specific to flashlights manufactured at the time of its publication.

Contents herein do not constitute a warranty.

Copyright Eveready Battery Co. Inc. - All Rights Reserved