



Single In-Line "Snap SIP" Socket Strips



Terminal Type -01 Shown



Features:

- Breakable at .100" (2.54mm) increments.
- Multiple finger contacts for reliability.
- Tapered entry for ease of insertion.
- Closed bottom sleeve for 100% anti-wicking of solder.

Terminals and Contacts:

Terminal: Brass - Copper Alloy (C36000), ASTM-B-16

Contact: Beryllium Copper - Copper Alloy (C17200), ASTM-B-194

Solder Preform:

63% Tin, 37% Lead

Plating:

Terminal: Gold over Nickel or Tin-Lead over Nickel


Contact: Gold over Nickel or Tin-Lead over Nickel

Body Material:

SS/LSS - Glass Filled Thermoplastic Polyester (P.B.T.) U.L. Rated 94V-O, -60°C to 140°C (-76°F to 284°F)

HSS/HLSS - High Temp. Glass Filled Thermoplastic, U.L. Rated 94V-O, -60°C to 260°C (-76°F to 500°F)


Terminal Information



 Quick turn delivery available on standard terminal types.

Additional terminal types available.
See terminal section for detailed terminal information.

Solder Preform Terminals Available on HSS and HLSS Body Types



See page 81 for complete details.

How To Order

