




LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
AD	25				H	EC 0010-1434-95	1/18/96	RAP
					J	EC 0010-1486-95	4/1/96	CR
					K	REV PER EC 001B-0367-00	04 JAN 01	CR

- 1 HOUSING MATERIAL: GLASS-FILLED POLYESTER. COLOR: GRAY.
- 2 CONTACT MATERIAL: PHOSPHOR BRONZE.
- 3 CONTACT FINISH: 0.00076[.000030] GOLD IN CONTACT AREA. 0.00127[.000050] NICKEL UNDERPLATE ALL OVER. TIN-LEAD ON POSTS.
- 4 PART NUMBER, DATE CODE IDENTIFICATION, CSA LOGO IN THIS APPROXIMATE AREA.
- 5 POINT OF MEASUREMENT FOR GOLD.
- 6 ACTION PIN POSTS REQUIRE 1.57[.062] MIN THICK PC BOARD. RECOMMENDED PC BOARD HOLES ARE Ø1.151±0.02[.0453±.001] DRILLED HOLE WITH 0.02-0.07[.001-.003] COPPER AND 0.008[.0003] MIN TIN-LEAD PLATING. FINISHED HOLE AFTER PLATING, Ø0.94-1.09[.037-.043].
- 7 CONTACT FINISH: DIN 41612 CLASS 3 IN CONTACT AREA. 0.00127[.000050] NICKEL UNDERPLATE ALL OVER. TIN-LEAD ON TAILS.
- 8 CONTACT FINISH: DIN 41612 CLASS 2 IN CONTACT AREA. 0.00127[.000050] NICKEL UNDERPLATE ALL OVER. TIN-LEAD ON TAILS.



SECTION X-X



PC BOARD LAYOUT

OBSOLETE SUPERSEDED BY 535080-5	7	1 THRU 50	X	X	X	150	535080-9
	8	1 THRU 50	X	X	X	150	535080-5
	3	1 THRU 50	X	X	X	150	535080-4
NOTES	POSITIONS LOADED		C	B	A	NO. OF LOADED POSITION	ASSY PART NUMBER
			ROWS LOADED				

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES - ON : 1 PLC DEC ± - 2 PLC DEC ±0.13[.005] ANGLES ± -	DR L. BRINER	2/16/89	AMP AMP INCORPORATED Harrisburg, Pa. 17105			
	CHK R.L. BRANDT	7/13/94				
	APPD R.L. BRANDT	7/13/94	NAME EUROCARD, RECEPTACLE ASSEMBLY, TYPE "C", TOOLLESS PRESSFIT			
	APPD R.L. BRANDT	7/13/94				
MATERIAL HSG CONT	PRODUCT SPEC -		SIZE D	CAGE CODE 00779	DRAWING NO 535080	
FINISH CONT	APPLICATION SPEC -		SCALE 4:1		SHEET 1 OF 1	
	WEIGHT -					