

main menue



home
test & measurement
products
skills
download

online catalogue T&M

clamp-type test probes
crocodile clips
 ▶ 0,64 mm system
 ▶ 2 mm system
 ▶ 4 mm system
 ▶ 4 mm safety system
test probes
oscilloscope test probes
measuring leads
plugs
sockets
sets
miscellaneous

company

portrait
corporate association
location maps
fairs and exhibitions
jobs
imprint
terms and conditions

Home ▶ crocodile clips ▶ crocodile clips ▶ AK 2 S


AK 2 S

datasheet for AK 2 S
article number: 932146101



[View Full-Size Image](#)



product description:	Bestellnummer: 932 146-101
description:	Insulated, high strength alligator clip. Clamping range up to 9.5 mm bolt diameter. The flat part of the jaws (fine wire section) allows even the finest wires to be clamped. 4 mm diameter socket connection and screw connection up to 1.5 mm².
typ:	AK 2 S rot/red
system:	4 mm system
order number:	932 146-101
clamping range:	9.5 mm
color versions:	
technical data	
type of contact:	clamp
type of termination:	4 mm socket (unsprung), screw
rated voltage:	30 VAC / 60 VDC
rated current:	25 A
contact resistance:	10 mOhm
material	
contact material:	brass
contact surface material:	nickel
housing material:	PP
environmental conditions:	
temperature range:	-25 °C to +80 °C
flammable class:	
housing:	UL 94 HB
drawing	



search online catalogue

Search

Messetermine

SPS/IPC/DRIVES
24. 11. 2015 - 26. 11. 2015

QR-Code

