


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED FOR PRODUCTION	12/14/01	TJC
B	ECN1509: ADDED PRODUCT VALIDATION	9/19/03	DFP
C	ECN1879: UPDATE DIMENSIONS 1.2 WAS 1.21; 1.6 WAS 1.58	10/7/04	DFP
.	.	.	.



RJ12 JACK
(6 X 6)

WIRING TABLE	
RJ12	LEAD COLOR
1	WHITE OR GRAY
2	BLACK
3	RED
4	GREEN
5	YELLOW
6	BLUE

SPECIFICATIONS
MOLDED PARTS ARE UL94V-0 RATED



MATERIAL:
HOUSING: MOLDED ABS
COLOR: DARK GRAY

D-SUB
INSULATOR: UL94V-0 THERMOPLASTIC
CONTACTS: GOLD PLATED
SHELL: TIN FINISH


RJ45
CONTACTS: GOLD PLATED, 50 μINCHES

NOTES:


- ADAPTOR KIT PROGRAMMED AS NEEDED BY INSERTING AND SEATING EACH PIN INTO DESIRED POSITION IN D-SUB CONNECTOR.



MALE 9-POSITION
CRIMP & POKE
D-SUB CONNECTOR



6X MALE CRIMP & POKE PINS



ASSEMBLED KIT

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
.X ±.1
.XX ±.05
.XXX ±.005
CABLE LENGTH TOLERANCE
<300" ±5% >300" ±2%

APPROVALS	DATE
DRAWN BY TJC	12/14/01
CHECKED BY DFP	12/14/01
APPROVED BY CM	12/14/01

CONFIGURATION DETAILS OF
UNDIMENSIONED FEATURES
MAY VARY

L-com CONNECTIVITY PRODUCTS		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
PRODUCT DESCRIPTION DB9M TO RJ12 MODULAR ADAPTOR		DRAWING TITLE OUTLINE DRAWING	
SIZE A	FSCM NO. 43321	DWG. NO. REC096M-OD1	REV. C
SCALE: NONE		CAD FILE: REC096M-OD1.SLDDRW	
		SHEET 1 OF 1	