


Wamco Part No.	Envelope Size	Base Type	Rating	Filament Shape
WL-755	T-3¼	BA9s	6.3V .15A	C-2R

Test Volts	Current (A)			Light Output (MSCP)			Life Hours
	Min.	Nom.	Max.	Min.	Nom.	Max	
6.3	.135	.150	.165	.247	.330	.413	20,000 Hrs.

Dimensional Characteristics:

1. L.C.L = .78" (19.8mm)
2. Base = Nickel-plated Brass Construction
3. ANSI Standard. No. 755
4. Part Mark: WL-755



RoHS Compliant

			Title:	
			T-3¼ Miniature Bayonet Base Lamp	
			6.3V .150A Vacuum	
Drawn	01/24/12	SL	Notes: Unless otherwise specified, all dimensions are in mm.	Rev: 1
Checked	01/24/12	EB		
Approved	01/24/12	EB		