


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED FOR PRODUCTION	8/16/01	TJC
B	ECN 3223: CN RELEASE	3/10/08	D.FRISIELLO
C	ECN 99999: ADDED FAMILY SERIES CODE	3/24/08	D.FRISIELLO
D	ECN 3923: ADDED WIRE MAP, REVISED NOTES, NEW FORMAT	4/7/09	D.FRISIELLO



WIRING MAP		
"P1"	WIRE COLOR	"J1"
1	BLACK	1
2	BROWN	2
3	RED	3
4	ORANGE	4
5	YELLOW	5
6	GREEN	6
7	BLUE	7
8	PURPLE	8
9	GRAY	9
10	WHITE	10
11	PINK	11
12	LIGHT GREEN	12
13	BLACK/WHITE	13
14	BROWN/WHITE	14
15	RED/WHITE	15
SHELL	DRAIN WIRE	SHELL

MODEL NUMBER	LENGTH	
	FEET	METERS
CHD15MF-2.5	2.5	.76
CHD15MF-5	5.0	1.52
CHD15MF-7.5	7.5	2.29
CHD15MF-10	10.0	3.05
CHD15MF-15	15.0	4.57
CHD15MF-25	25.0	7.62



NOTES:

INTERNAL 360° FOIL SHIELDS IN CONNECTOR HOODS CONNECTED TO CABLE DRAIN WIRE AND CONNECTOR FRAMES.

CONNECTOR PINS: GOLD PLATED.

CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.

CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN A POLY BAG.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.3 .XX = ±.15 PROJECTION 	APPROVALS		DATE		 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845
	DRAWN BY TJC		8/8/01		
	CHECKED BY DFP		8/15/01		CATEGORY
	APPROVED BY RC		8/16/01		DATA CABLES
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		PRODUCT DESCRIPTION HD15M/F DATA CABLE ASSEMBLY			
COLOR VARIATIONS MAY OCCUR		SIZE A	FSCM NO. 43321	DWG. NO. CHD15MF	REV. D
CHD-FS01		SCALE: NONE		CAD FILE: CHD15MF.SLDDRW	SHEET 1 OF 1