








SOLDER LUG



SWITCH FUNCTION

	POS. 1	POS. 2	POS. 3
Model No.			
MFS 126	ON	NONE	ON
Term. Conn.	2-1	OPEN	2-3

Specifications:

Contact rating:	0.4VA max.; 20V max. (AC or DC)
Contact resistance:	10mOhm max. at 2-4V DC
Insulation resistance:	1 000MOhm min.
Dielectric strength:	1 000V RMS
Operating temperature:	-30°C to +85°C
Mechanical life:	30 000 make-and-break cycles
Material:	Case: diallyl phthalate (DAP) (UL94V-0) Actuator: nylon, black Housing: stainless steel Contact: gold plated



Tolerances: 0.00: ± 0.25mm 0.0: ± 0.40mm			Date	Name	MFS 126 DB	
			03/08	dr		
					30 14 24	
Modifications	Date	Name	knitter-switch		Page 1/1	