Thomas&Betts





Standard Barrel Copper Lug

T&B Catalog Number: 54111UF
UPC Number: 78621016499
Status: Active
Description:

Copper One-Hole Lug, 45 Degree Bend, Standard Barrel, Peep Hole, Max 35kV, Wire Size 3/0 AWG, 3/8 Inch Bolt Size, Tin Plated, Die Code 50, Die Color Code Orange

General

Material	Copper
Finish	Tin Plated
Wire Size	3/0 AWG
Number of Studs	1
Stud Size	3/8
Tongue Angle	45
Barrel Length	Standard
Barrel Shape	Standard
Tongue Width	Standard
Peep Hole	Y
Marking	Standard
Hole Shape	Round
Die Color	Orange
Die Code	50

Dimension Information

A (inches)	1.969
B (inches)	.813
C (inches)	.938
D (inches)	.141
E (inches)	.625
F (inches)	.375

Specifications

Voltage Rating	600V to 35KV

Tooling

Connector & Tooling Chart	Available on Website

Packaging

T&B Order Multiple	100
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	6.25 lbs. per 100

Application Support

Overview	Available on Website

Notes

Dimensions given for reference only. Dimensions may vary up to .030.

Certifications

RoHS Compliance	Yes

Certifications

File Nbr:

E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com