

GT4 SERIES FOR NICHIA 119 / 219 LEDs





- Special care taken to make a uniform white or warm white illumination.
- Lens material optical grade PMMA. Allows use of high current and temperature conditions (105°C/220°F)
- Best available optical efficiency, up to 90%.
- Please check fastening details from this link:
(http://www.ledil.com/datasheets/DataSheet_GLUES.pdf)
- Diameter 35mm (MR11).

LENS TYPES

NAME	ORDERING CODE	FWHM
GT4 SMOOTH SPOT	C10971_GT4-N19-S	±9°
GT4 MEDIUM	C10972_GT4-N19-M	±14°
GT4 WIDE	C10973_GT4-N19-W	±18°
GT4 WW	C10974_GT4-N19-WW	±31°



MEASUREMENT DATA

Relative Intensity of C10971_GT4-N119-S





© Ledil Oy – PRELIMINARY - Subject to change without prior notice

Relative Intensity of C10972_GT4-N119-M





© Ledil Oy – PRELIMINARY - Subject to change without prior notice

Relative Intensity of C10973_GT4-N119-W




© Ledil Oy – PRELIMINARY - Subject to change without prior notice

Relative Intensity of C10974_GT4-N119-WW



© Ledil Oy – PRELIMINARY - Subject to change without prior notice

DRAWINGS



© Ledil Oy – PRELIMINARY - Subject to change without prior notice

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Ledil:](#)

[C10971_GT4-S](#) [C10972_GT4-M](#) [C10973_GT4-W](#) [C10974_GT4-WW](#) [C10971_GT4-N119-S](#) [C10972_GT4-N119-M](#)
[C10973_GT4-N119-W](#) [C10974_GT4-N119-WW](#)