

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301100033](#)
Status: **Active**
Overview: [Wide-Area Lighting Products](#)
Description: Wet Location 70W HPS Magnet Mount Area Light with Feed Thru, Cord Type 16/3 SJTOW, Cord Length 3.04m (10.0')

Documents:
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
UL E174254

General
Product Family Portable Lighting
Series [130110](#)
NEMA Configuration NEMA 5-15
NEMA Rating NEMA 3
Outlet Feed-Through
Overview [Wide-Area Lighting Products](#)
Product Name Woodhead
Type Wide Area Lamps
UPC 78678829571

Physical
Cord Length - Primary 3.04m (10.0')
Cord Length - Secondary 0.305m (1.0')
Depth 207.26mm (8.160")
Duty Wet Location
Guard Included No
Guard Type N/A
Height 264.16mm (10.400")
Length 228.60mm (9.000")
Material - Globe Clear Polycarbonate
Material - Guard N/A
Mounting Style Magnet
Packaging Type Carton
Socket Construction N/A

Electrical
Bulb Type High Pressure Sodium
Cord Type - Primary 16/3 SJTOW
Cord Type - Secondary 16/3 SJTOW
Lamp Type HPS
Lamp Wattage - Maximum 70W
Lumens 4300
On/Off Switch No
Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info
Engineering Number 8565F



Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130110 Series](#)