


#4-40 UNC-2B X .250  
DEEP FAR SIDE  
(4 PLACES)



# SPECIFICATIONS

FREQUENCY RANGE: 2 TO 500 MHz  
 NUMBER OF OUTPUT PORTS: 4  
 MINIMUM ISOLATION: 22 dB  
 MAXIMUM VSWR: 1.35  
 MAXIMUM INSERTION LOSS: 1.50 dB



**PASTERNAK ENTERPRISES, INC.**

P.O BOX 16759, IRVINE, CA 92623  
 PHONE (949) 261-1920 FAX (949) 261-7451

WEB ADDRESS: [www.pasternack.com](http://www.pasternack.com)  
 E-MAIL ADDRESS: [sales@pasternack.com](mailto:sales@pasternack.com)

**COAXIAL & FIBER OPTICS**

DWG TITLE

**PE2045**

DES.

N FEMALE POWER DIVIDER, FREQUENCY  
 RANGE: 2-500 MHz 4 OUTPUT PORTS

SIZE A

**FSCM NO. 53919**

CAD FILE

120406

SCALE N/A

127

NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.