



Search Results

Evaluate

- FAQ's

How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click to remove) Search Tips

Text Search: 'HSTTV12-M4'

Your search criteria matched only one product, shown below

HSTTV12-M4



Flexible Polyolefin VW-1 DRY-SHRINK™ Heat Shrink Tubing in Bulk Reels

- For dry locations
- Highly flame retardant Meets UL VW-1 Rating
- Fast Shrink Time
- Material Type: Highly Flexible Crosslinked Polyolefin
- Shrink Ratio: 2:1
- Temperature Range: -67°F to 257°F (-55°C to 125°C)
- Voltage: 600V
- UL VW-1 Recognized, CSA Certified
- Mil Spec: AMSDTL-23053/5 Class 3

	Part Number	HSTTV12M4
	RoHS Compliancy Status	Compliant
	Part Description	Thin Wall Polyolefin Heat Shrink (UL224 VW1)
	Material	Polyolefin cross-linked
	Color	Yellow
	CSA Certified	Yes
	Military Specification	AMS-DTL-23053/5 Class 3
	UL Recognized	E122770
	Length (m)	304.8
	CE Compliant	No
	CE Marking	No
	Flammability Rating	UL224 VW-1
	Length Per Reel (ft.)	1000
	Length Per Reel (m)	304.8
	Max. Recovered I.D. (In.)	.062
	Max. Recovered I.D. (mm)	1.6
	Min. Expanded I.D. (In.)	.125
	Min. Expanded I.D. (mm)	3.2
	Nominal Diameter (In.)	.125
	Nominal Diameter (mm)	3.2
	Nominal Recovered Wall Thickness (In.)	.02
	Nominal Recovered Wall Thickness (mm)	0.5
	Pricing Description	Heat Shrink Thin VW1, .12"(3.2mm) Dia, Yellow
	Shrink Ratio	2:1
	Temperature Range	-67°F to 257°F (55°C to 125°C)
	Min. Order UOM	RL
	Min. Order Qty.	1
	BOM Qty. (# of Pkgs.)	0
	Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.