



Type 360291

Single terminal block, solderable, horizontal wire entry, lift system, with molded housing, double solder pins, screw brought down by hand (transport safety)

Technical Data

RIA V / A / AWG 50 / 15 / 22 - 14

SP V / A / AWG 50 / 15 / 22 - 14

Insulation co-ordination according to EN 60664-1

Tightening torque UL 4.4 lb-in max.

Solder pin dimension 2 x 1.0 mm

Recommended pc board hole dia. Ø 1.5 mm

Solder pin length 3.5 mm

Type 360271

Single terminal block, solderable, horizontal wire entry, lift system, with molded housing, single solder pin, screw brought down by hand (transport safety)

Technical Data

RIA V / A / AWG 50 / 15 / 24 - 16

SP V / A / AWG 50 / 15 / 24 - 14

Insulation co-ordination according to EN 60664-1

Tightening torque UL 4.4 lb-in max.

Solder pin dimension 1.2 mm


Recommended pc board hole dia. Ø 1.5 mm

Solder pin length 2.9 mm

Color black

Dimensions in mm

1 mm = 0.0394 in.




Part numbers (P/N)

Type 360291

P/N 360291

Dimensions in mm

1 mm = 0.0394 in.



Part numbers (P/N)

Type 360271

P/N 360271