

### FWZ Series FWZ55

FWZ 36, 53, and 55 Hour Meters are rectangular flush panel mount designed to fit into tight locations. All can withstand IP54

environmental rating (requires use of gasket).



#### Specifications:

- Bezel: 2.36" x 1.36" (60 x 34.5mm)
- Capacity: 99.999.99 hours
- Digits: 7 – 0.16" high numerals
- Voltage: 24, 120, 240, 50 or 60Hz models
- Power Consumption: 1VA
- Temperature: –40° to 160°F (–40° to 72°C)
- Termination: Combination 1/4" spade and screw clamp.  
Rear access  
screw terminals available (model "K")
- Weight: 1.8oz
- Flush panel retainer mounted with slip-on plastic retaining bracket
- Panel Opening: 2.06" x 1.08" rectangular (52 x 27.5mm)