





REV.	DATE	DESCRIPTION
NC	03/26/01	INITIAL RELEASE



DESCRIPTION		MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS		APPROVALS		DATE	 Connector Corporation TNC CRIMP PLUG (REVERSE THREADS) (FOR RG 8/U, 213/U CABLE)			
1	BODY	BRASS	NICKEL	DIMENSIONS IN [] ARE IN INCHES FOR CUSTOMER REFERENCE ONLY		DRAWN	G.R.S.	03/26/01				
2	INSULATOR	TEFLON	NATURAL			CHECKED						
3	CONTACT PIN	BRASS	GOLD	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5-6 = ± 0.2 6-30 = ± 0.4 30-120 = ± 0.6		ISSUED						
4	FERRULE	BRASS	NICKEL									
5												
6				120-315 = ± 1								
7				315-1000 = ± 1.6								
8				1000-2000 = ± 2.4								
DO NOT SCALE DRAWING												
TITLE		TNC CRIMP PLUG (REVERSE THREADS) (FOR RG 8/U, 213/U CABLE)		SIZE		FROM NO.		DWG. NO.		REV.		
A		99001				122394RT.DWG		NC				
SCALE		NA		PART NO.		122394RT		SHEET		1 OF 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[122394RT](#)