

WCY55

WCY55

WCY55 : WEJTAP CONN YEL



ACTIVE

RoHS compatible

BURNDY® PRODUCTS

Assistant

Add to Favorites

Email Datasheet

Print Datasheet

FCI Brings You More

Contact our sales/technical support

Sample request

Price request

Specifications

Download document

Dimensional	Physical	Approvals / Certifications	Other Features
Dimensional			
Conductor Size (Run - Diameter)	0.537 to 0.75		
Conductor Size (Run - mm)	14 mm² to 19 mm²		
Conductor Size (Run)	3975		
Conductor size (Tap - Max)	2668		
Conductor size (Tap - Min)	250		
Conductor Size (Tap)	250 266.8		
Conductor Type (Run)	AAC		
Wire Size	AWG		
Wire Size (Tap - Diameter - in)	0.499 to 0.714		
Wire Size (Tap - mm)	13 mm² to 18 mm²		
Wire Type (Tap)	AAC Copper		
Physical			
Color Code	Yellow		
Approvals / Certifications			
UL Listed	No		
CSA Certified	No		
Other Features			
Installation Tool	WTRB WTY		
Booster	WPBY Box 25		
UPC	78181087415		
Keyword	wejtap		