

D-SUB cable - VS-25-DSUB-20-LI-1,0 - 1656291

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Assembled D-SUB cable shielded, 25-pos., stranded (7-wire), cable color RAL 7000 (gray), IP20 degree of protection, head 1 with socket shell 3 and straight cable outlet, head 2 with pin shell 3 and straight cable outlet, length: 1 m



Key commercial data

Packing unit	1 pc
Weight per Piece (excluding packing)	172.6 GRM
Custom tariff number	85444290
Country of origin	China

Technical data

Mechanical characteristics

Number of positions	25
Insertion/withdrawal cycles	≥ 50
Cable exit	Straight
Length of cable	1 m

Ambient conditions

Ambient temperature (operation)	0 °C ... 70 °C
Degree of protection	IP20

Material data

Housing material	PVC
Contact material	Copper alloy
Contact surface material	Gold-plated
Outer sheath, material	PVC

Electrical characteristics

Rated voltage (III/3)	125 V
-----------------------	-------

D-SUB cable - VS-25-DSUB-20-LI-1,0 - 1656291

Technical data

Electrical characteristics

Rated current	1 A
---------------	-----

Classifications

eCl@ss

eCl@ss 4.0	27060306
eCl@ss 4.1	27060306
eCl@ss 5.0	27061801
eCl@ss 5.1	27061801
eCl@ss 6.0	27061801
eCl@ss 7.0	27061801
eCl@ss 8.0	27061801

ETIM


ETIM 2.0	EC000830
ETIM 3.0	EC001855
ETIM 4.0	EC001855
ETIM 5.0	EC001855

UNSPSC


UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Drawings

Dimensioned drawing




Dimensioned drawing




D-SUB cable - VS-25-DSUB-20-LI-1,0 - 1656291

Circuit diagram



Schematic diagram



Schematic diagram

