


Crimphousing for Pin Contacts 3,00 mm

Series

434



Rated current	5,0 A
Rated voltage	250 VRMS / VDC
Withstand voltage	1500 VRMS for 1 minute
Material contact	Copper alloy
Material insulator	Thermoplast UL94V-0
Operating temperature	-40°C to +105°C

All dimensions in mm.

pitch
3,00max.
pincount
024


Variation

Contact


Series

605

AWG 20 - 24



1

Plating:
T = SnPackaging:
L = Bulk
R = Reel


Plating contact

Packaging (L,R)


605-1-TX-X

Crimp Tool

454



454-1-06



2

no. of contacts	see figure left	see figure left	available in variation
n	A	B	
002	6,85	3,00	1
003	9,85	6,00	1
004	12,85	9,00	1
005	15,85	12,00	1
006	18,85	15,00	1
007	21,85	18,00	1
008	24,85	21,00	1
009	27,85	24,00	1
010	30,85	27,00	1
011	33,85	30,00	1
012	36,85	33,00	1
002	3,85	-	2
004	6,85	3,00	2
006	9,85	6,00	2
008	12,85	9,00	2
010	15,85	12,00	2
012	18,85	15,00	2
014	21,85	18,00	2
016	24,85	21,00	2
018	27,85	24,00	2
020	30,85	27,00	2
022	33,85	30,00	2
024	36,85	33,00	2

Variation (1,2)

No. of contacts

Order code:

434-1-0000-X-KS0

www.mpe-connector.de