



Short Arm Hex L-keys Nickel Finish



Nickel-Plated

- Ideal for use in clean rooms & other environments where non-oxidizing surfaces are specified or required.



351 Metric L-wrench Hex Key, Short Arm, high alloy CVM steel, hardened, nickel plated. Precision machined, burr free chamfered ends.

Item No.	mm	mm	Inch	mm	Inch	lbs.	pkg.
351 04	1.5	45	1.8	14	.6	.01	10
351 08	2.0	49	1.9	16	.6	.01	10
351 12	2.5	55	2.2	18	.7	.01	10
351 16	3.0	61	2.4	20	.8	.02	10
351 20	4.0	68	2.7	25	1.0	.03	10
351 24	5.0	78	3.1	28	1.1	.04	10
351 28	6.0	88	3.5	32	1.3	.07	10
351 32	7.0	92	3.6	34	1.3	.10	10
351 36	8.0	97	3.8	36	1.4	.13	10
351 40	9.0	103	4.1	38	1.5	.18	10
351 44	10.0	109	4.3	40	1.6	.23	10
351 45	12.0	122	4.8	45	1.8	.40	1
351 75	14.0	137	5.4	56	2.2	.61	1
351 77	17.0	156	6.1	63	2.5	1.02	1
351 79	19.0	176	6.9	70	2.8	1.40	1



Nickel-Plated

- Ideal for use in clean rooms & other environments where non-oxidizing surfaces are specified or required.



351 Inch L-wrench Hex Key, Short Arm Nickel-plated

Item No.	Inch	mm	Inch	mm	Inch	lbs.	pkg.
351 43	.050	40	1.6	10	.39	.01	10
351 46	1/16	46	1.8	14	.55	.01	10
351 47	5/64	50	2.0	16	.63	.01	10
351 50	3/32	52	2.1	19	.75	.01	10
351 52	7/64	54	2.1	19	.75	.01	10
351 53	1/8	58	2.3	21	.83	.02	10
351 55	9/64	62	2.4	23	.91	.02	10
351 56	5/32	68	2.7	25	.99	.02	10
351 59	3/16	70	2.8	26	1.0	.04	10
351 62	7/32	77	3.1	29	1.2	.05	10
351 65	1/4	88	3.5	31	1.2	.08	10
351 68	5/16	98	3.9	36	1.4	.13	10
351 71	3/8	107	4.2	38	1.5	.20	10
351 74	1/2	133	5.2	44	1.7	.46	1
351 76	9/16	158	6.2	64	2.5	.64	1
351 78	5/8	175	6.9	71	2.8	.85	1
351 80	3/4	198	7.8	89	3.5	1.40	1



351 91 Metric Hex L-wrench Set, 9 Pc. in Plastic Holder

Equipped with 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0, 10.0mm

lbs. .59 pkg. 1



351 93 Metric Hex L-wrench Set, 6 Pc. in Plastic Holder

Equipped with 1.5, 2.0, 2.5, 3.0, 4.0, 5.0mm


lbs. .20 pkg. 1



351 92 Inch Hex L-wrench Set, 8 Pc. in Plastic Holder

Equipped with 5/64, 3/32, 1/8, 5/32, 3/16, 7/32, 1/4, 5/16"

lbs. .41 pkg. 1



351 94 Inch Hex L-wrench Set, 13 Pc. in Plastic Holder

Equipped with .050 - 3/8"

lbs. .72 pkg. 1