




(2,54 mm) .100"

PGP SERIES



POGO STYLE ONE PIECE CONNECTOR

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?PGP

Insulator Material:

Black LCP

Contact Material:

Brass

Plating:

Au over 30µ" (0,76 µm) Ni

RoHS Compliant:

Yes


Processing:

Lead-Free Solderable:






Yes

SMT Lead Coplanarity:

(0,10 mm) .004" max



PGP	1	NO. OF POSITIONS	01	PLATING OPTION	ROW OPTION	ALIGNMENT PIN	OPTION
		02 thru 05		-G = 10µ" (0,25 µm) Gold	-S = Single Row -D = Double Row	-AT = Alignment Top Side -AD = Alignment Top And Bottom	-P = Pick & Place Pad -TR = Tape & Reel



Note: Some lengths, styles and options are non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 SAMTEC NORTH CAROLINA • Tel: 408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: 1-800-726-8329
 SAMTEC AMERICA LATINA COMERCIO EXTERIOR LTDA • Tel: (+55 31) 3786 3227 SAMTEC UNITED KINGDOM • Tel: 44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
 SAMTEC FRANCE • Tel: 33 01 60 95 06 60 SAMTEC ITALY • Tel: 39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46-84477280 SAMTEC BENELUX • Tel: 44 01236 739292
 SAMTEC ISRAEL • Tel: 972-3-7526600 SAMTEC INDIA • Tel: +91-80-3272 1612 SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 SAMTEC JAPAN • Tel: 045-475-1385 SAMTEC CHINA • Tel: 86-21-6083 3766
 SAMTEC TAIWAN • Tel: 886-2-2735-6109 SAMTEC HONG KONG • Tel: 852-26904858 SAMTEC KOREA • Tel: 82-31-717-5685 SAMTEC ANZ • Tel: 613 9580 0683