






REV.	DATE	DESCRIPTION
NC	02/24/03	INITIAL RELEASE



- NOTE:
1. CRIMPED FERRULE
HEX CRIMP SIZE .128"
 2. CONTACT PIN TO SOLDER

8	HEAT SHRINK TUBE			1	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex PART DESCRIPTION SMB R/A CRIMP JACK (FOR RG-174/U, 188A/U, 316/U CABLE)					
7	FERRULE	COPPER	GOLD	1		DRAWN	G.R.S.						02/24/03
6	COVER	BRASS	GOLD	1		CHECKED							
5	INSULATOR	P.E.	NATURAL	1		ISSUED			PART NO. 142252				
4	INSULATOR	TEFLON	NATURAL	1		SHEET	1 OF 1						
3	CONTACT PIN	BRASS	GOLD	1					DWG. NO. 142252.DWG REV. NC SIZE A SCALE NA				
2	BARREL	BRASS	GOLD	1									
1	BODY	BRASS	GOLD	1									
	DESCRIPTION	MATERIAL	FINISH	QTY			CAD FILE	C:/142/142252.DWG					