



## Speed, Performance, Value - The Right Balance

- RS-232 interface
- Internal counting resolution 1:400,000
- Preset tare function
- Full range tare
- Zero Tracking
- Memory accumulation
- Adjustable filters
- Pre-set counting with alarm
- Date and time
- Large backlit LCD displays
- Simple user-friendly operation
- Precision load cell technology
- Splashproof to protect from accidental spills
- Full colour coded keypad with numeric entry
- Large stainless steel pan
- Easy to use keypad
- Non-slip adjustable feet
- Overload protection
- Easy access to the rechargeable battery
- External calibration
- Rechargeable battery up to 90 hours operation
- Auto sleep / power down function to save battery life
- Low battery indication
- AC Adapter
- Weighing
- Weight accumulation
- Parts counting
- Check counting
- Count accumulation



## Technical Specifications

| Model                | CBC 4     | CBC 8 | CBC 16        | CBC 32 | CBC 48 |
|----------------------|-----------|-------|---------------|--------|--------|
| Maximum capacity     | 4000g     | 8000g | 16kg          | 32kg   | 48kg   |
| Readability          | 0.1g      | 0.2g  | 0.5g          | 1g     | 2g     |
| Tare range           | -4kg      | -8kg  | -9.9995kg     | -32kg  | -48kg  |
| Repeatability (S.D.) | 0.1g      | 0.2g  | 0.5g          | 1g     | 2g     |
| Linearity (±)        | 0.2g      | 0.4g  | 1g            | 2g     | 4g     |
| Pan size             | 225×275mm |       |               |        |        |
| Units of measurement | Gram (g)  |       | Kilogram (kg) |        |        |

## General Specifications

|                              |                                                                        |
|------------------------------|------------------------------------------------------------------------|
| Internal counting resolution | 1:600,000                                                              |
| Functions                    | Parts counting, weighing, memory accumulation, preset count with alarm |
| Typical stabilisation time   | 2 Sec                                                                  |
| Calibration                  | Automatic External                                                     |
| Display                      | 3 x 6 digits LCD digital displays                                      |
| Power supply                 | Rechargeable battery or mains power                                    |
| Operating temperature        | 0°C - 40°C                                                             |
| Housing                      | ABS plastic, stainless steel platform                                  |
| Overall dimensions (wxdxh)   | 315×355×110mm                                                          |
| Net weight                   | 4.1kg                                                                  |

## Key Accessories

- In-use Cover
- In-Use Cover pack of 10
- Adam Printer
- Thermal Paper Roll for Adam Printer
- AdamDU - Data Collection Program
- RS-232 to PC Cable
- In-Use Cover pack of 5
- RS-232 to USB Interface Cable (must be ordered with 3074010266 RS232 cable)
- Hard Carry Case with Lock
- ATP Thermal Printer
- Thermal Paper for ATP



Adam Equipment - offices worldwide

[www.adamequipment.com](http://www.adamequipment.com)