

Coaxial Cable Connector 16_MCX-50-2-102/111_NH-1

Description

Right angle cable plug

Interface standards
IEC 60169-36_CECC 22220



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	6 GHz

Mechanical Data

Centre contact	soldered
Outer contact	soldered
Weight	0.0007 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00006023
Catalogue drawing	DOU-00006025
Assembly instruction	DOC-0000179237

Ordering Information

Bulk 100 pcs package	16_MCX-50-2-102/111_NH-1
----------------------	--------------------------

Additional Information

Suitable cables	RG_316/_U, ENVIROFLEX_316, RG_188_A/U
-----------------	---------------------------------------