


DO NOT SCALE
DIMENSIONS IN mm


METRIC

THIRD ANGLE
PROJECTION



NOTES:

- PRODUCT SPECIFICATION: 108-19041
- PACKAGING: ON PLASTIC TUBES, BOXED



$$\pm 0,25 \\ C = (N-1) \times 2,54 + 8,6 = 21,3$$

$$\pm 0,2 \\ B = (N-1) \times 2,54 + 5,1 = 17,8$$

$\pm 0,2$
13,4


BOARD TO BOARD
CONTACT POST FOR
0,8min DIA HOLE

2,54

$$(N-1) \times 2,54 = 12,7$$

$3,2 \pm 0,2$

0,5max



CONTACT: 0,4µm MIN SELECTIVE
GOLD PLTD ON MATING CONTACT
AREA AND 3,0µm MIN TIN PLTD
ON CONTACT POST, OVER 1,25µm MIN
Ni PLTD UNDERLAYER

HOUSING: THERMOPLASTIC
POLYESTER 20% GF, UL94-V0
COLOUR GREEN
CONTACT: 1 PH. BRONZE H06

166086-6

CUSTOMER
DRAWING

FOR REFERENCE ONLY
WILL NOT BE UPDATED

tyco
Electronics

tyco Electronics AMP Italia S.p.A.
C.so F.lli Cervi, 15 - Collegno (TO)

THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION JULY 1986

© COPYRIGHT 1986 BY AMP-HOLLAND B.V.
ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE
COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

H2	ET00-0047-04	D.C.	C.T.	05MAR2004
H1	ET00-0115-03	D.C.	C.T.	24JUN2003
H	ET00-0068-03	P.B	D.C	9-5-03
G	-	-	-	12-6-89
LTR.	REVISION RECORD	DR.	CHK.	DATE

DR. C. SOUSA	DATE 08-07-86
CHK. J. BROEKSTEEG	DATE 08-07-86
APP. L. V. SOEST	DATE 09-07-86

WIRE RANGE	NAME	6 POS. AMP-EDGE CONN., 2.54 PITCH SINGLE LOADED WITH B. T. B. CONTACTS		
INSUL. RANGE				
SIZE A3	SHEET 1 OF 1	DRAWING NO	C-166086	REV. LTR. H2

8

7

6

5

4

3

2

1