

D-Series







The D-Series toggle switches are single pole and have ratings up to 20 amps and 1-1/2 horsepower. These switches have a nylon toggle and base, and are also available with integrated wire leads.


- Specifications**
- Certifications*: UL, CSA
 - Dielectric Strength: 1,000 V (minimum)
 - Insulation Resistance: 100 Megohms (minimum)
 - Base Material: Nylon
 - Actuator Material: Nylon
 - Bushing Material: Polycarbonate

* Due to ongoing technological advances, consult factory for certification specifics.

Dimensional Specifications: in. [mm]



 SOLDER LUG	 .250 TAB (Q.C.)	 INTEGRATED WIRE LEAD (no exposed conductors)
TERMINAL TYPE		



D	A	22	1	-	P	B	-	B
SERIES		RATING	TERMINATION		TOGGLE STYLE			TOGGLE COLOR¹
D SINGLE POLE TOGGLE		10 5A 250VAC 10A 125VAC 1/2HP 125-250VAC	0 SOLDER LUG 1 .250TAB (QC) 5 WIRE LEAD		B BAT 	B BLACK W WHITE		
CIRCUIT		11 5A 250VAC 10A 125VAC						BUSHING¹
A ON-NONE-OFF		22 10A 250VAC 20A 125VAC 1 1/2HP 125-250VAC			P PADDLE 	B BLACK W WHITE		
B ON-NONE-ON		23 10A 250VAC 20A 125VAC						
C ON-OFF-ON		60 3A 250VAC 6A 125VAC 1/4HP 125-250VAC						

NOTES:
Shading indicates standard configurations.
Available with neoprene seal. Consult factory.
1 Custom colors are available. Consult factory.