








REV.	DATE	DESCRIPTION
A	11/04/10	RELEASE TO MFG.



RECOMMENDED MOUNTING
HOLE DIMENSIONS



RECOMMENDED
PCB LAYOUT

NO	DESCRIPTION	MATERIAL	FINISH	QTY	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.	APPROVALS	DATE	AMPHENOL CONNEX			
7	HEX NUT	BRASS	NICKEL	1	UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020" DO NOT SCALE DRAWING	DRAWN	CLEMENT	11/04/10	PART DESCRIPTION		
6	LOCK WASHER	BRASS	NICKEL	1		CHECKED			BNC END LAUNCH RECEPTACLE PLUG		
5	INSULATOR	TEFLON	NATURAL	1		ISSUED			PUSH ON, 75 OHMS		
4	HOUSING	BRASS	NICKEL	1		SHEET	1 OF 1		PART NO.		
3	CONTACT PIN	BRASS	GOLD	1					112770-10		
2	INSULATOR	TEFLON	NATURAL	1					DWG. NO.		
1	BODY	BRASS	NICKEL	1					112770-10.DWG		
									REV. A		
									SIZE A		
									SCALE NA		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[112770-10](#)