


TO-18 Metal Can - Clear Epoxy - 120 deg Angle

INDEX

PRODUCT TREE



SPEC! Image next to part no. indicates cad file.

- [Product Table](#)
- [Table Footnotes](#)
- [Order Samples](#)
- [Stock/Price Request](#)
- [Sales and Tech Support](#)

- [Product Gallery](#)
- [Opto-Electronic Components](#)
- [Photo Diodes](#)
- [Radial Leaded Packages](#)
- [TO-18 Metal Can - Clear Epoxy - 120 deg Angle](#)

Lumex drawings are in PDF format. If you don't have Adobe Acrobat, click on this icon to

[download a free copy](#)



Lumex Part Number	Lens	Vr Max (V) *	Pd Max (mW) *	t-opr (deg C) *	Voc mV Typ	Isc microA Typ	Id nA Max @ Vr=10V	lambda p (nm) Typ.	lambda theta deg	lambda nM	tr/tf Vr=10V RI=1000 ohms
OED-SP-1ML SPEC!	Clear Epoxy	5	20	- 20 ; + 85	400	15	100	900	+/- 60	450 ; 1050	6/6 nS

Table Footnotes

[\[top of page\]](#)

- * Limits of Safe Operation

[Home](#) |
 [What's New](#) |
 [Product Gallery](#) |
 [Product Search](#) |
 [X-Ref Search Engine](#) |
 [Tech Notes](#) |
 [Sales and Tech Support](#) |
 [Corporate Info](#)

290 East Helen Road Palatine, IL 60067 Telephone: (847) 359-2790 Facsimile: (847) 359-8904 E-mail us at sales@lumex.com

