




CONNETTORE TIPO A (CON MOLLA DI RITEGNO ESTERNA)  
CONNECTOR TYPE A (WITH EXTERNAL SPRING)

SCALA NON IMPEGNATIVA  
(DO NOT SCALE)  
DIMENSIONI IN mm  
(DIMENSIONS IN)

METRIC

PROIEZIONE EUROPEA  
(EUROPEAN PROJECTION)



ASSE CONNETTORE  
(CONNECTOR CENTER LINE)

ASSE CAVITA'  
(CAVITY CENTER LINE)

TIP. CAVITA' PER TERMINALI AMP JPT P/N 929939-...  
OPPURE 929937-... E RELATIVI GOMMINI  
P/N 828904-1, 828905-1, 282536-1.  
TAPPO CAVITA' P/N 828906-2  
(TYP. CAV. FOR JPT CONT. P/N 929939-... A/O 929937-... AND REL.  
SINGLE WIRE SEAL P/N 828904-1, 828905-1, 282536-1  
CAVITY PLUG P/N 828906-2)

| ROSSO (RED)      | ---               |              |              |                                        |                                   |                                |
|------------------|-------------------|--------------|--------------|----------------------------------------|-----------------------------------|--------------------------------|
| GIALLO (YELLOW)  | ---               |              |              |                                        |                                   |                                |
| MARRONE (BROWN)  | 282192-3          | N            | 3            | \\\\\\\\\\\\                           | ACCIAIO INOX<br>(STAINLESS STEEL) | MOLLA (SPRING)                 |
| BLU (BLUE)       | ---               |              |              |                                        |                                   |                                |
| VERDE (GREEN)    | ---               |              | 2            | NATURALE<br>(NATURAL)                  | GOMMA (RUBBER)                    | GUARNIZIONE<br>(RUBBER GASKET) |
| NATURALE (NATUR) | ---               |              |              |                                        |                                   |                                |
| GRIGIO (GREY)    | 282192-2          | N            | 1            | \\\\\\\\\\\\                           | PA 6.6                            | BLOCCETTO<br>(HOUSING)         |
| NERO (BLACK)     | 282192-1          |              |              |                                        |                                   |                                |
| COLORE<br>COLOR  | NUMERO<br>PART N° | ASSY<br>REV. | N°<br>(ITEM) | FINITURA / COLORE<br>(FINISH / COLOUR) | MATERIALE<br>(MATERIAL)           | DESCRIZIONE<br>(DESCRIPTION)   |

CUSTOMER DWG.  
FOR REFERENCE ONLY

DISEGNO PER CLIENTE  
SOLO PER RIFERIMENTO

THIS DRAWING IS UNPUBLISHED RELEASE FOR PUBLICATION

TOLLERANZE, SE NON  
DIVERSAMENTE SPECIFICATO  
(TOLERANCES, UNLESS  
OTHERWISE SPECIFIED)

DIAM. ISOLANTE  
(INS. DIA. RANGE)  
1.5-3.0  
(REDUCED INS. CABLE)

RANGO FILO  
(WIRE RANGE)  
0.5-2.5 mm<sup>2</sup>

SCALA  
(SCALE)  
\*\*\*

± 0.3  
ANGOLI  
(ANGLES) ± 2°

DIS. NOV. 9. '90  
(COR.)  
Ennio CINI


**TE** TE Connectivity  
DESCRIZIONE  
(DESCRIPTION)  
4 W. SPLASH PROOF CONN. ASS'Y  
with SECONDARY LOCK

|      |                                |              |                |
|------|--------------------------------|--------------|----------------|
| N    | ECR-14-003472                  | MP           | 24MAR14        |
| M2   | REVISED PER ECO-11-005033      | RK           | 5APR11         |
| REV. | REVISIONI<br>(REVISION RECORD) | DIS.<br>(DR) | DATA<br>(DATE) |




|                                     |
|-------------------------------------|
| CONT. 13 OCT 92<br>(CHK) C. TARTARI |
| APP. (APP.)                         |

|           |                    |      |                   |
|-----------|--------------------|------|-------------------|
| LOC. SIZE | NUMERO<br>(DWG NO) | REV. | FOGLIO<br>(SHEET) |
| I A3      | C-282192           | N    | 1 D1<br>(COP) 2   |


PASSO 5.0±0.15 TIP.  
(PITCH 5.0±0.15 TYP.)



DISTRIBUZIONE  
(PRINT DIST.)




DETT. TAB - SCALA 5:1  
(TAB DETAIL)



- 1 QUOTE APPLICABILI PER SFORMATURA PEZZO (DRAFT PERMITTED TO FACILITATE REMOVAL OF PART FROM THE MOULD)
- 2 MATERIALE LINGUETTE: LEGA DI RAME STAGNATA, ES. OTTONE STAGNATO. (TAB CONTACT MATERIAL: TIN PLATED COPPER ALLOY. E.G. BRASS TIN PLATED)
- 3 MATERIALE BLOCCHETTO: TERMOPLASTICO CARICATO FIBRA VETRO. (HOUSING MATERIAL: THERMOPLASTIC, GLASS FIBER FILLED)

FORMA ALTERNATIVA PERMESSA CON RAGGIO  
(ALLOWED ALTERNATIVE PROFILE WITH RADIUS)



|                                                                                               |  |                                                        |  |                            |  |
|-----------------------------------------------------------------------------------------------|--|--------------------------------------------------------|--|----------------------------|--|
| FINITURA / COLORE<br>(FINISH / COLOUR)                                                        |  | MATERIALE<br>(MATERIAL)                                |  | NUMERO<br>(PART NUMBER)    |  |
| CUSTOMER DWG.<br>FOR REFERENCE ONLY                                                           |  | DISEGNO PER CLIENTE<br>SOLO PER RIFERIMENTO            |  |                            |  |
| THIS DRAWING IS UNPUBLISHED                                                                   |  |                                                        |  | RELEASE FOR PUBLICATION    |  |
| TOLLERANZE: SE NON<br>DIVERSAMENTE SPECIFICATO<br>(TOLERANCES: UNLESS<br>OTHERWISE SPECIFIED) |  | DIAM. ISOLANTE<br>(INS. DIA. RANGE)                    |  | RANGO FILO<br>(WIRE RANGE) |  |
| ± 0.3                                                                                         |  | ---                                                    |  | ---                        |  |
| ANGOLI<br>(ANGLES)                                                                            |  | ---                                                    |  | SCALA<br>(SCALE)           |  |
| ± 2°                                                                                          |  | ---                                                    |  | ---                        |  |
| DIS.<br>(DR.)                                                                                 |  | DESCRIZIONE (DESCRIPTION)                              |  |                            |  |
| CONT.<br>(CHK)                                                                                |  | 4 POS. SPLASH PROOF CONN. ASS'Y<br>with SECONDARY LOCK |  |                            |  |
| APP.<br>(CAP.)                                                                                |  | LOC. SIZE<br>(DWG NO)                                  |  | REV. FOGGIO<br>(SHEET)     |  |
| SEE SHEET 1 OF 2                                                                              |  | I A3                                                   |  | N 2                        |  |
| REV. REVISIONI<br>(REVISION RECORD)                                                           |  | DIS. DATA<br>(DR. DATE)                                |  | NUMERO<br>(DWG NO)         |  |
|                                                                                               |  |                                                        |  | C-282192                   |  |