


IEC 60320 C14 Inlet

161-R30148-E

KOBICONN

IEC 60320 C14 Inlet



Dimensions: mm

Materials

Body: Black Glass-Fiber Thermoplastic

SPECIFICATIONS

Rating: 10A, 250VAC
Insulation Resistance: Over 100MΩ at 500VDC
Dielectric Strength: 2000VAC for 1 minute
 RoHS Compliant

Tolerance

X.XX±0.1
 XX.XX±0.2
 XXX.XX±0.3

Date Last Revised: 8-20-07

Available from Mouser Electronics
 1-800-346-6873 / www.mouser.com

KC- 301181

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

161-R30148-E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-R30148-E](#)