


6mm Round Swage Standoff


Lyn-Tron Part ID: **BR5115B-08.0-43**

Qty Available: **0**

Pricing & Availability:	Click to obtain pricing for: BR5115B-08.0-43
CAD Drawings:	View CAD Drawing (Internet Explorer Only)
	Download CAD Drawing (Right Click and Save Target As... to download)
	Download Autodesk Design Review© 2010
Conformity Statement:	View conformity statement: BR5115B-08.0-43

General Notes

- Material: Please visit our [material specifications](#) section for additional information.
- Shank Length: Please visit our [shank lengths](#) section for additional information.
- Standard Finishes:**
 - Zinc (Clear Chromate; Plate ID - 34) on brass and steel material.
 - Iridite (Gold Plate ID - 26) on aluminum material.

Material Code	Material Description
☐ AA	Aluminum (RoHS Compliant)
☐ AL	Aluminum
☒ BR	Brass (RoHS Compliant)
☐ SS	Stainless Steel (RoHS Compliant)
☐ ST	Steel (RoHS Compliant)

Basic Part No.	Thread Size
☐ 5114	M3.0 x 0.5
☒ 5115	M3.5 x 0.6

Shank Code	Panel Thickness	Shank Length (0.080)
☐ A	0.8	1.90
☒ B	1.6	2.70
☐ C	2.4	3.40
☐ D	3.2	4.20

Length Code	Length Value
☐ 03.0	3
☐ 04.0	4
☐ 05.0	5
☐ 06.0	6
☒ 08.0	8
☐ 10.0	10
☐ 11.0	11

Applicable finishes based on material code -- BR

☐ 00	Plain - None
☐ 03	Bright Dip ? Brass
☐ 31	Cadmium Clear Chromate - QQ-P-416, CL 2