Search Results

Evaluate
- FAQ's
How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click ☒ to remove) Search Tips

☒ Text Search: 'F612D5-5F287Y'

Your search criteria matched only one product, shown below

F612D5-5F287Y

- Pass all TIA/EIA-568-B.3 performance requirements
- FOCIS-5 compliant
- Insertion loss per mated pair: .50dB typical; .75dB max.
- Factory terminated, assembled and 100% tested for insertion loss
- Insertion loss data recorded for every multimode cable assembly
- Lifetime traceability of test data to a Q.C. number on each cable assembly
- 2-pin alignment assures consistent repeatable performance

* MTP is a registered trademark of US Conec Ltd.

Part Number	F612D5-5F287Y
RoHS Compliancy Status	RoHS directive is not applicable
Note	Intended for use in fixed installations which are outside the scope of RoHS
Part Description	Female MTP* to female MTP* twelve strand fiber optic cable assembly (one female MTP* connector on each end on ribbon interconnect cable) 62.5/125µm. Outside diameter: 5mm x 2.5mm.
Product Type	MTP* 12 Fiber Interconnect Cable Assemblies
Length (ft.)	287
Length (m)	87.5
Fiber Compatibility	62.5/125µm
Fiber Type	Multimode
Cable Color	Orange
Cable Type	Duplex
CE Compliant	No
Connector 1 Type	MTP* Connector
Connector 2 Type	MTP* Connector
End Configurations	MTP* to MTP*
Fiber Count	12
Flammability Rating	Plenum (OFNP)
Pricing Description	287 ft – MTP*-MTP* Plenum Interconnect Cable Assembly 62.5µm
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	☐

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.

Copyright © 1995-2012, PANDUIT CORP. All rights reserved. | Legal Information | Privacy Policy