



YAV26-L1_BOX

2/0 HVYDTY RING 1/4 STUD

ACTIVE



Electrical division

☒ [Email Datasheet](#) ☒ [Print Datasheet](#)

FCI Brings You More

- ☒ [Contact our sales/technical support](#)
- ☒ [Sample request](#)
- ☒ [Price request](#)

Download document

Literature

- ☒ [> Power solutions Product Focus](#)
- ☒ [> INSULUG Brochures](#)
- ☒ [> Renewable Energy Products Brochure](#)
- ☒ [> EC&M Catalog](#)
- ☒ [> Connector Theory and Application Brochure](#)

Application Tooling

- ☒ [> Electrical Tooling](#)

Specifications

Dimensional	Physical	Approvals / Certifications	Other Features
Dimensional			
Strip length (Wire)			13/16 in.
Stud Hole (Size)			1/4 in.
Tongue Angle			Straight
Tongue Width (in)			0.93 in.
Wire Shroud			No
Physical			
Conductor Size			2/0 AWG
Conductor Type			Commercial/Military Stranded Copper
Insulation Type			Bare
Conductor Size (Range)			2/0 AWG
Approvals / Certifications			
Military Listed			MS20659-153
UL Listed			Yes
CSA Certified			Yes
Other Features			
Tongue Type			Ring
Bulk Catalog Number			YAV26-L1
UPC			78181054020
Keyw ord			smtermHD