

Model P230
24mm Rotary Potentiometer
Conductive Plastic Element
500,000 Cycle Life
Metal Shaft
Brass Bushing
RoHS Compliant



MODEL STYLE

Side Adjust , Solder Lugs

P230

ELECTRICAL¹

Resistance Range, Ohms	500-1M
Standard Resistance Tolerance	± 20%
Residual Resistance	20 ohms max.
Input Voltage, maximum	500 Vac max.
Power rating, Watts	0.5W- B taper, 0.25W-others
Dielectric Strength	500Vac, 1 minute
Insulation Resistance, Minimum	100M ohms at 250Vdc
Sliding Noise	100mV max.
Actual Electrical Travel, Nominal	260°

MECHANICAL

Total Mechanical Travel	300°± 10°
Static Stop Strength	70 oz-in
Rotational Torque	0.5 to 1.25 oz-in


ENVIRONMENTAL

Operating Temperature Range	-20°C to +70°C
Rotational Life	500,000 cycles

¹ Specifications subject to change without notice.

Model P230

ORDERING INFORMATION²




Shaft Types

E-TYPE							F-TYPE						M-TYPE						Q-TYPE					
L	15	20	22	25	30	35	L	15	20	25	30	35	L	16	19	25	30	35	L	16	19	25	30	35
T	7	12	12	12	12	12	T	7.5	7.5	12	12	12	T	6	6	12	12	12	T	6	6	12	12	12

Shaft Position (F-Type Shaft)

Dashed lines on Type "C" and Type "A" shows position of adjustment slot for E-Type shaft




STANDARD RESISTANCE VALUES, OHMS

500 1K 2K 5K 10K 20K 50K 100K 200K 500K 1MEG


² Contact our customer service for custom designs and features.

Model P230

OUTLINE DRAWING



CIRCUIT DIAGRAM



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TT Electronics:

[P230-DEC22BR20K](#) [P230-CEC22BR20K](#) [P230-2EC22BR20K](#) [P230-1EC20AR20K](#) [P230-3FA25BR1K](#) [P230-1EC20BR20K](#) [P230-2FA25BR10K](#) [P230-1FC25BR5K](#) [P230-1FD20BR10K](#) [P230-1FD20BR150K](#) [P230-2EC20BR10K](#) [P230-1FC15AR10K](#) [P230-2QC19BR250K](#) [P230-1EC15BR100K](#) [P230-3EC20B500K](#) [P230-2EC20AR1MEG](#) [P230-1EC15AR250K](#) [P230-3MC19BR500K](#) [P230-2EC20AR1M](#) [P230-2FC20BR500K](#) [P230-1FC20AR250K](#) [P230-2MC16CR500K](#) [P230-2MC16AR250K](#) [P230-1MC16AR250K](#) [P230-2FC15AR10K](#) [P230-2MC16BR500K](#) [P230-1FC15BR10K](#) [P230-1FC35BR100K](#) [P230-2EC20AR50K](#) [P230-1FC25BR100K](#) [P230-1FC20AR500K](#) [P230-2EC20AR500K](#) [P230-2MC16BR300K](#) [P230-1FC25AR500K](#) [P230-1EC15AR1MEG](#) [P230-2EC35BR25K](#) [P230-2FC15BR10K](#) [P230-2EC20AR250K](#)