

Item # LC1D32U7, TeSys D IEC Contactor - 32A - Vac Coil



TeSys D IEC Contactor - 32A - Vac Coil

TeSys D IEC Contactor - 32A - 240Vac Coil

SPECIFICATIONS

|                         |                         |
|-------------------------|-------------------------|
| Termination Method      | Screw Clamp             |
| Contact Rating          | 600V / 32A              |
| Coil Voltage            | 240Vac 50/60 Hz         |
| 50/60 Hz Voltage Code   | U7                      |
| Coil Consumption Inrush | 70 VA                   |
| Coil Consumption Sealed | 7.5 VA                  |
| Power Wire Size         | #6 - #14 AWG            |
| Power Terminal Torque   | 20 lb-in (2.5 Nm)       |
| Control Wire Size       | #10 - #18 AWG           |
| Control Terminal Torque | 15 lb-in (1.7 Nm)       |
| Mounting Hardware       | 35mm DIN Rail, #8 screw |
| Weight                  | 0.83 lb (0.375 kg)      |
| AC1 Resistive Rating    | 50 Amp                  |
| AC3 Inductive Rating    | 32 Amp                  |
| AC3 Single Phase 115V   | 2 HP                    |

|                                  |                 |
|----------------------------------|-----------------|
| AC3 Single Phase 230V            | 5 HP            |
| AC3 Three Phase 200V             | 10 HP           |
| AC3 Three Phase 230V             | 10 HP           |
| AC3 Three Phase 460V             | 20 HP           |
| AC3 Three Phase 575V             | 30 HP           |
| Control Contact Rating (1NC/0NO) | A600            |
| UL File/CCN                      | E164862 / NLDX  |
| CSA File                         | LR43364 3211 04 |
| Meets Standard                   | IEC 60647-4     |
| CE                               | Yes             |
| RoHS                             | Yes             |