







# Gecko Connectors

## Cable Connectors – Individual Contacts

- ❖ 4-finger Beryllium Copper contact on a female connector.
- ❖ Ready for assembling to housings on page 8.
- ❖ Crimp barrel meets all crimp guidelines and standards.
- ❖ 2A current capacity, resists high vibration and shock.
- ❖ Withstands extremes of temperature: -65°C to +150°C.



GECKO

<b>FEMALE SINGLE ENDED</b>	<b>FEMALE – FEMALE</b>
	
<b>MALE SINGLE ENDED</b>	<b>MALE – MALE</b>
	
<b>MALE – FEMALE</b>	<b>TOOLS</b>
	<b>Contact Insertion/Removal Tool</b> – Z125-902 See page 12 ❖ Instruction sheets available at <a href="http://www.harwin.com/downloads/instructions">www.harwin.com/downloads/instructions</a>

### HOW TO ORDER

**G125 - X WX XXXX X 94**

#### SERIES CODE

#### GENDER – FIRST END

<b>M</b>	Male
<b>F</b>	Female

#### CABLE SIZE

<b>W1</b>	26 AWG
<b>W2</b>	28 AWG
<b>W3</b>	30 AWG
<b>W4</b>	32 AWG

#### CABLE COLOUR

<b>94</b>	White
-----------	-------

#### TERMINATION – SECOND END

<b>L</b>	Loose cut end
<b>F</b>	Female
<b>M</b>	Male

#### CABLE LENGTH

<b>0150</b>	150mm
<b>0300</b>	300mm (double-ended)
<b>0450</b>	450mm (single-ended)

All dimensions in mm.

Patent Pending – UK 1205109.0