




1. MATERIAL:
HOUSING: 30% GLASS FILLED PBT, THERMOPLASTIC, BLACK.
CONTACT: PHOS BRONZE
2. FINISH: CONTACT PLATING TIN (LEAD FREE); 60 UIN MIN. OVER 30 UIN MIN.
SOLDERABILITY :95% COVERAGE MIN.;
WORKING CONDITION:230°±5°C MAX
3. MECHANICAL SPECS:
DURABILITY: 50 CYCLES MIN.
INSERTION FORCE:300 GRAMS MAX.
WITHDRAWAL FORCE: 20 GRAMS MIN.
CONTACT RETENTION: 500 GRAMS MIN.
ACCEPTS: 0.20-0.30 [.008-.012] LEADS
4. ELECTRICAL SPECS:
VOLTAGE RATING: 250V AC,DC
CONTACT RESISTANCE: 20 MILLOHMS MAX.
CURRENT RATING: 1 AMPERE AC,DC
INSULATION RESISTANCE: 1000 MEGOHMS MIN.
DIELECTRIC WITHSTANDING VOLTAGE: AC 1000 V MIN.
5. OPERATING TEMPERATURE: -40°C TO +105°C
6. TE LOGO

		2		32		48.10		40.64		1-2199300-2	
		FINISH		POS		B±0.15		A±0.20		PART NO.	
THIS DRAWING IS A CONTROLLED DOCUMENT.						OWN WINNING WANG CHK SIMON LI APVD COREL WANG		 TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± 0.2(.008) 3 PLC ± — 4 PLC ± — 4 FPC ANGLES ± —				NAME DIP SOCKET, 15.24 CENTERLINE OTC STYLE —					
		FINISH				WEIGHT —		SIZE A1		CAGE CODE 100779	
MATERIAL 		 				CUSTOMER DRAWING		DRAWING NO C2199300		RESTRICTED TO —	
						SCALE 5:1		SHEET 1 of 1		REV A	