

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0395151420

Status:

Obsolete

Description:

3.81mm (.150") Pitch Eurostyle™ Vertical PCB Header, with Threaded Retention Inserts and Reverse Imprinting, 20 Circuits

Documents:

Drawing (PDF)

General

Product Family	Terminal Blocks
Series	39515
Application	Wire-to-Board
Comments	with Reverse Imprinting
Component Type	PCB Header
Product Name	ESE, Eurostyle™ Pluggable
Type	Euro Block

Physical

Circuits (Loaded)	20
Entry Angle	N/A
Lock to Mating Part	Yes
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.50mm (.138")
PCB Thickness - Recommended	2.50mm (.098")
Panel Mount	No
Pitch - Mating Interface	3.81mm (.150")
Pitch - Termination Interface	3.81mm (.150")
Polarized to Mating Part	Yes
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-40°C to +105°C
Wire Size AWG	N/A


Electrical

Current - Maximum per Contact	8A
Voltage - Maximum	300V

Material Info

Reference - Drawing Numbers

Product Specification	PS-39500-001
Sales Drawing	SD-39501-002, SD-39515-001



EU RoHS

ELV and RoHS
Compliant

REACH SVHC

Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product
environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

39515Series

Mates With

Most 3.81mm (.150") Pitch Industry
Standard Plugs, 39517 Vertical Plug with
Retention Screws, 39514 Horizontal Plug
with Retention Screws

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION