



Connectors, reducers and couplers

• HG-T T-Connector, IP66

T-connector with inspection lid.

Features and Benefits

- Fast fit T-connector
- With inspection lid
- High pull-off strength
- Highly resistant to solvents and oils
- Free of halogen, sulphur and phosphorus



HelaGuard HG-T, T-Connector, IP66.

Technical Table

Article-No.	Type	Entry nominal diameter	Exit nominal diameter	Pack Cont.
166-24800	HG16-T	16	16	5
166-24801	HG20-T	20	20	3
166-24802	HG21-T	21	21	3
166-24803	HG28-T	28	28	3
166-24804	HG34-T	34	34	2
166-24805	HG42-T	42	42	2

All dimensions in mm. Subject to technical changes.

Colour grey available on request.

Material Data

Material	Polyamide 6.6 (PA66)
Colour	Black (BK)
Operating Temperature	-50 °C to +135 °C
Flammability	UL94 V2



• HGL-T T-Connector, IP68

T-connector with conduit seals.

Fulfills IP66, IP67, IP68 and IP69k.

Features and Benefits

- Fast fit T-connector
- With inspection lid and additional seals
- High pull-off strength
- Highly resistant to solvents and oils
- Free of halogen, sulphur and phosphorus



HelaGuard HGL-T, T-Connector with conduit seals.

Technical Table

Article-No.	Type	Entry nominal diameter	Exit nominal diameter	Pack Cont.
166-24900	HGL16-T	16	16	5
166-24901	HGL21-T	21	21	3
166-24902	HGL28-T	28	28	3
166-24903	HGL34-T	34	34	2
166-24904	HGL42-T	42	42	2

All dimensions in mm. Subject to technical changes.

Colour grey available on request.



Please note! Not all products listed on this page may have this approval.
For product specific approvals please refer to the Appendix.