




Units:mm



Electrical test:
1. 100% short, open, miswire test
2. Conduct resistance: 5 Ohm(max)
3. Insulation resistance: 10Mohm(min)
4. dielectric test: DC 300V

⑧	TIE	2	BLACK L=80mm
⑦	PE BAG	1/10	CLEAR SIZE: 280*330*0.05mm PRINT BLACK"MADE IN CHINA"+"10PCS"
⑥	PE BAG	1	CLEAR SIZE: 130*230*0.05mm PRINT BLACK"MADE IN CHINA"+"1PC"
⑤	S/R	3.0g	BLACK PVC 40P (Mould NO.:SR-048)
④	IN JACKET	1.6g	CLEAR LD-PE (Mould NO.:NM-006)
③	OUT JACKET	6.6g	PVC-40P RED(RD-35),(Mould NO.:WM-009)
②	OUT JACKET	1.6g	CLEAR LD-PE (Mould NO.:NM-006)
①	CABLE	1	NOUL 28#(10/0.10+28/0.10)*2F JACKET BLACK OD2.8*5.6mm
NO.	CONN	4	RCA PLUG MALE 梅花型 TYPE NI-PLATED INSULATOR COLOR:BROWN
NAME QTY SPECIFICATION			
4			

Cnc Tech, LLC			
Industrial Cable and Connector Technology			
DRAWN BY	LICHENG	DRAWING NO.	
CHECKED BY		CUSTOMER	
APPROVAL BY		ITEM NO.	770-20011-00100
DECIDE BY		DATE	2012-12-17
VERSIONS/EDITEON	A/0	PROJECTION	