





## HEYClip™ Tension Wire Clips

### Adhesive-Backed

- Gather and direct cables singly or in groups smaller than those accommodated by other Heyco Wire Holders.
- WCA-5 may also be screw mounted. #6 screws not included.
- Nylon 6/6 with a 94V-2 flammability rating.

| WIRE CAPACITY          |            | PART NO.<br>Natural | DESCRIPTION | FOOTPRINT   |             | OVERALL HEIGHT |      |
|------------------------|------------|---------------------|-------------|-------------|-------------|----------------|------|
| in.                    | mm.        |                     |             | in.         | mm.         | in.            | mm.  |
| .125 x .250            | 3,2 x 6,4  | <b>3638</b>         | WC A-4      | .63 x .63   | 15,9 x 15,9 | .25            | 6,4  |
| .125 x .500            | 3,2 x 12,7 | <b>3639</b>         | WC A-5      | 1.00 x 1.13 | 25,4 x 28,6 | .31            | 7,9  |
| <b>BUNDLE DIAMETER</b> |            |                     |             |             |             |                |      |
| .190                   | 4,8        | <b>3629</b>         | WC A-43     | .63 x .63   | 15,9 x 15,9 | .31            | 7,9  |
| .250                   | 6,4        | <b>3636</b>         | WC A-44     | .63 x .63   | 15,9 x 15,9 | .38            | 9,5  |
| .375                   | 9,5        | <b>3637</b>         | WC A-46     | .75 x .75   | 19,1 x 19,1 | .50            | 12,7 |

Standard color natural.



*Quick  
Specs*

Material  
Flammability Rating

Nylon 6/6  
94V-2

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[3895](#) [3893](#) [3900](#) [3889](#)