



Save as PDF



2720 LED Headlight



- Gesture Activation Control
- Variable Light Output
- Dual Red LED Night Vision

Gloved hands, wet hands or oily hands are not an issue when using the 2720 with **Gesture Activation Control** technology. Turn on the light with a wave of a hand. Additional features include: Low level red light that preserves night vision, for nighttime applications. Signaling red (S.O.S) beacon light. Optical 4x magnification allows for a wide or penetrating beam,. Including a variable light output from 100%-10%.



2720 LED Headlight ANSI FL1 Specifications

LIGHT SOURCE.	High	
	LED	
BATTERIES	3 AAA Alkaline (Included)	
CHARGE TIME		
VOLTAGE	4.5	
LENGTH	6.3 cm (2.48")	
WEIGHT W/ BATTERIES	0.13 kg (4.5 oz.)	
WEIGHT W/O BATTERIES	0.07 kg (2.6 oz.)	

Materials

Body	Lens	Shroud	Switch Type
ABS	PC		
Clip	Contact, Spring & Retainer	O-Ring	Night Vision Film

Configuration

Cat. #	Description
2720	2720 LED Headlight

2720 LED Headlight Accessories

No accessories are currently available for this product

LIGHT
OUTPUT

RUNTIME
(hours/min)

BEAM
DISTANCE
(meters)

PEAK BEAM
INTENSITY
(candela)

FL 1 STANDARD	High	Low
	8h	
	56m	15 m.
	790cd	60cd