



FOR REAR MOUNTED MATING CONNECTORS
PANEL THICKNESS 1-2mm FOR SAFE CONTACT AREA



ØF = Cable diameter

max. torque are 40 Ncm
Mounting instruction AM0268
Part-No. 8 and 9 not mounted

② Protection standard IP67, 100% checked
according to DIN EN 60529



9	Cable clamp screw	Steel	zinc plated
8	Cable clamp	Steel	zinc plated
7	Shielding plate	Bronze	tin plated
6	Nut	Polyamide	nickel plated
5	Pressure washer	Polyester	nickel plated
4	Seal ring	Elastomer	black
3	Locking screw with o-ring seal	FVSW1/5-K1449 4-40 / Brass + Elastomer	nickel plated + red
2	O-ring seal	Elastomer	red
1	Hood	FWA1GA, FWA2-5GA-K201 / Polyester	nickel plated
No. St. Part		Type Description/Material	Surface plating/Colour/Class

Measurement without tolerance acc. to ISO 2768-m		SCALE	TITLE
NAME / DATE		2:1	
DRAWN		Gabriele Wagner	
CHECKED		Arno Meyer-Richter	
		01-02-2013	
3	30-01-2013	23381	FWA1-5GA
2	26-09-2008	22309	
1	04-06-2008	22244	
REV.	DATE	CH.-NO.	
		FWA1GA-2GA, FWASGA, SW	PAGES 1

Order-No.	Shell Size / for No. of Contacts	A	B	C	D	E	øF	G	H	J	K	L	M	N	P
FWA1GA	1 / 9	20.2	25	39.8	36.4	16.5	6 - 8	20	54 - 57.5	13	17	32.4	28.8	22.1	SW20
FWA2GA	2 / 15	20.2	33.3	48.5	36.4	16.5	6 - 8	28	54 - 58	13	25	41.1	28.8	26.6	SW24
FWA3GA	3 / 25	24	47	62.3	43.6	20.3	8 - 10.5	40	63 - 66.5	13	37	53.8	36	26.6	SW24
FWA4GA	4 / 37	24	63.5	78.6	52.1	20.3	8 - 10.5	56.2	71.5 - 75	13	53.2	71.1	44.5	26.6	SW24
FWA5GA	5 / 50	27.6	61.1	75.7	52.1	22	9 - 11	55.5	73.5 - 78.5	16	52.2	68	44.5	32.1	SW29